



## Measurement Conversion - Metric Volume Units (Common) with Decimals -

### Small to Base

|   |                                   |   |              |   |           |   |                                   |   |           |   |           |
|---|-----------------------------------|---|--------------|---|-----------|---|-----------------------------------|---|-----------|---|-----------|
| 1 | Convert this value to kiloliters  | A | 21 kl        | B | 2,100 kl  | 2 | Convert this value to hectoliters | A | 2.8 hl    | B | 28,000 hl |
|   | 21,000 l                          | C | 21,000 kl    | D | 210 kl    |   | 2,800 l                           | C | 0.28 hl   | D | 28 hl     |
|   |                                   | E | 2.1 kl       | F | 0.21 kl   |   |                                   | E | 280 hl    | F | 2,800 hl  |
| 3 | Convert this value to centiliters | A | 21 cl        | B | 21,000 cl | 4 | Convert this value to hectoliters | A | 0.024 hl  | B | 24 hl     |
|   | 0.21 l                            | C | 2,100 cl     | D | 0.21 cl   |   | 2,400 l                           | C | 2.4 hl    | D | 240 hl    |
|   |                                   | E | 2.1 cl       | F | 210 cl    |   |                                   | E | 24,000 hl | F | 2,400 hl  |
| 5 | Convert this value to liters      | A | 0.22 l       | B | 2.2 l     | 6 | Convert this value to liters      | A | 2,500 l   | B | 0.25 l    |
|   | 22 cl                             | C | 0.0022 l     | D | 22 l      |   | 25 dl                             | C | 25 l      | D | 0.0025 l  |
|   |                                   | E | 220 l        | F | 0.022 l   |   |                                   | E | 2.5 l     | F | 250 l     |
| 7 | Convert this value to liters      | A | 230,000 l    |   |           | 8 | Convert this value to liters      | A | 0.0026 l  | B | 0.26 l    |
|   | 23 kl                             | B | 230 l        |   |           |   | 26 cl                             | C | 0.00026 l | D | 2.6 l     |
|   |                                   | C | 23,000 l     |   |           |   |                                   | E | 26 l      | F | 0.026 l   |
|   |                                   | D | 23 l         |   |           |   |                                   |   |           |   |           |
|   |                                   | E | 2,300 l      |   |           |   |                                   |   |           |   |           |
|   |                                   | F | 23,000,000 l |   |           |   |                                   |   |           |   |           |